

Antenna socket insert (UD2415ST)

| Specification | Order No. | Packing unit | PS | EAN |
|---------------|-----------|--------------|----|---------------|
| | 0042 00 | 1/5 | 01 | 4010337042006 |

Features

- 2-gang routing box in plug-in technology.
- IEC plug for FM (radio) and DVB-T/T2.
- IEC pin jack for DVB-S/S2 (SAT).
- DC feed-through from the SAT connection to the input and bidirectional circulation between input and output with bridging of the DC voltage.
- The internal conductor is connected simply by pressing it, without the need for screws. Internal conductor can thus be removed multiple times.
- Complies with shield class A.

Technical data

| | |
|---------------------------|-----------------|
| TV frequency band | |
| - Frequency range: | 5 to 862 MHz |
| - Decoupling: | > 40 dB |
| - Transmission loss: | 1.2 dB |
| - Attenuation: R/TV plug: | 13 dB |
| SAT frequency band | |
| - Frequency range: | 950 to 2400 MHz |
| - Decoupling: | > 35 dB |
| - Transmission loss: | 2 dB |
| - Attenuation: SAT plug: | 14 dB |
| Installation depth: | 27 mm |

Notes

- Suitable for terrestrial reception, area couplers, and satellite reception systems.
- For screw attachment only.