

Light bulb dimming insert with pressure/2-way switch

| Specification | Order No. | Packing unit | PS | EAN |
|---------------|-----------|--------------|----|---------------|
| 100 – 1000 W | 1181 00 | 1/5 | 02 | 4010337003939 |

Features

- Dimming light bulbs and HV halogen lamps at AC 230 V, 50 Hz.
- Electronic short-circuit protection.
- Automatic excess-temperature protection with restart.
- With screw terminals.

Technical data

| | |
|--------------------------|---------------------|
| Rated voltage: | AC 230/240 V, 50 Hz |
| Connected load at 25 °C | |
| - Light bulbs: | 100 to 1000 W |
| - HV halogen lamps: | 100 to 1000 W |
| Installation depth: | 32 mm |
| Connection cross section | |
| - maximum: | 2.5 mm ² |
| Ambient temperature: | +5 °C to +45 °C |

Notes

- If the ambient temperature is higher than 25 °C, the connected load must be reduced.