

**Door station, 1-gang  
TX\_44**

Specification	Order No.	Packing unit	PS	EAN
pure white	1260 66	1	18	4010337260660
anthracite	1260 67	1	18	4010337260677
colour aluminium	1260 65	1	18	4010337260653

**Features**

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX\_44 switch range.
- Modular design, therefore easy installation and expandability with further components such as call buttons, info module, colour camera, Keyless In.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.
- Binary input for connecting a zero-voltage push button (NO contact) as a call button.
- Call button, 1-gang

**Technical data**

Power supply:	via the 2-wire bus
Bus coupler connections	
- 2-wire bus:	2 x screw terminal

Illustrations are similar and may deviate from originals.

- Additional power supply:	2 x screw terminal
- Binary input:	2 x screw terminal
- Connection cable:	2 x connector strip
- Video:	1 x connector strip

#### Speech insert connections

- Connection cable:	2 x connector strip
---------------------	---------------------

Ambient temperature:	-25 °C to +70 °C
----------------------	------------------

Protection class:	IP44
-------------------	------

Installation depth:	30 mm
---------------------	-------

---

#### Dimensions in mm

Name plate:	B 62	H 62
-------------	------	------

---