

**Call button, 3 gang for door station
TX_44**

Specification	Order No.	Packing unit	PS	EAN
Program-neutral	1263 00	1	18	4010337263005

Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- The door station can be expanded with additional call buttons (up to 14 call button inserts, 1- or 3-gang can be connected to one door station).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate can be replaced without tools and without removing the frame.
- Professional inscription by the Gira inscription service www.beschriftung.gira.de or the Gira inscription software.

Technical data

Power supply:	via connection cable
Connecting the connection cable:	2 x connector strip
Protection class:	IP44
Ambient temperature:	-25 °C to +70 °C
Installation depth:	30 mm

Notes

- Call buttons which are not required can be covered with the call-button cover plate for call button, 3-gang.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Dimensions in mm

Name plates: B 62 H 18
