

## Surface-mounted door station, 3 gang

| Specification    | Order No. | Packing unit | PS | EAN           |
|------------------|-----------|--------------|----|---------------|
| pure white       | 1267 66   | 1            | 18 | 4010337267669 |
| anthracite       | 1267 67   | 1            | 18 | 4010337267676 |
| colour aluminium | 1267 65   | 1            | 18 | 4010337267652 |

### Features

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX\_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.
- Low installation height of just 19 mm.

### Technical data

Power supply: DC 26 V  $\pm$  2 V (by 2-wire bus)

Connections  
- 2-wire bus: 2 x screw terminal

Illustrations are similar and may deviate from originals.

|                            |                         |
|----------------------------|-------------------------|
| - Additional power supply: | 2 x screw terminal      |
| Protection class:          | IP44                    |
| Ambient temperature:       | -25 °C to +70 °C        |
| Dimensions                 |                         |
| - Door station, 1-gang:    | W 110 x H 181 x D 19 mm |
| - Name plates:             | W 62 x H 18 mm          |

---

## Notes

- Call buttons which are not required can be covered with the call-button cover plate for call button, 3-gang.
-