

Power supply DC 24 V 300 mA

Specification	Order No.	Packing unit	PS	EAN
DRA	1296 00	1	18	4010337296003

Features

- Power supply DC 24 V for external supply to the Gira One server.

Technical data

Rated voltage	
- Primary:	AC 230 V, 50/60 Hz
Secondary rated voltage	
- Secondary:	DC 24 V
Secondary rated current:	0.3 A
Fuse:	Fine wire fuse 250 V, T 125 mA
Ambient temperature:	-5 °C to +40 °C
Protection class:	IP 20

Dimensions

Modular width (MW):	4
---------------------	---