

**Gira energy profile with light element and 3 empty units height 769 mm  
not equipped**

Specification	Order No.	Packing unit	PS	EAN
anthracite	1349 28	1	17	4010337349280
colour aluminium	1349 26	1	17	4010337349266

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

**Features**

- Freely configurable Gira energy profile with 3 empty units and light element.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- The three empty units can be individually equipped with device inserts from the TX\_44 design line or from System 55 by the customer.

**Technical data**

Protection type (device cover closed): IP44

**Notes**

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Single wall plug mounting.
- Suitable for E27 light sources with energy efficiency classes A++ to E.

## Scope of supply

- Cover frame, 3-gang TX\_44 is included with delivery.
- The mounting materials are included with delivery.
- Light sources are not included with delivery.

---

## Dimensions in mm

Base:	B 229	H 10	T 155
Profile:	B 142	H 769	T 75

---