

## EnOcean wireless wall transmitter, 2-gang

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	2422 01	1	02	4010337060420
pure white glossy	2422 03	1	02	4010337060437
pure white matt	2422 27	1	02	4010337060451
anthracite	2422 28	1	02	4010337060468
colour aluminium	2422 26	1	02	4010337060444
black matt	2422 005	1	02	4010337037095
grey matt	2422 015	1	02	4010337084648

### Features

- Wireless transmitter for transmitting switching, dimming and blind commands to wireless receivers in the EnOcean wireless system.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Encrypted or unencrypted wireless transmission possible.

## Technical data

Wireless frequency:	868.3 MHz
Range	
- in free field:	up to 300 m
- in buildings:	approx. 30 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

---

## Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
- This product cannot be used with eNet. Gira EnOcean transmitters are compatible with third-party actuators.

---

## Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.