

RCCB 30 mA

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	2664 01	1	03	4010337011897
pure white glossy	2664 03	1	03	4010337011903
pure white matt	2664 27	1	03	4010337011910
anthracite	2664 28	1	03	4010337011927
colour aluminium	2664 26	1	03	4010337011934
black matt	2664 005	1	03	4010337037064
grey matt	2664 015	1	03	4010337085232

Features

- The RCD is a permanently installed protective device with voltage-dependent residual current tripping in accordance with VDE0664.
- This device works like an RCD switch.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Rated current:	16 A
Rated residual current:	30 mA
Installation depth:	32 mm
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature:	-25 °C to +40 °C

Notes

- Areas of application: Parapet trunking, in front of socket outlets or in Gira energy profile.
 - Mounting in a deep device box.
-