

## Rocker switch 10 AX 250 V~ with rocker, 2-gang for hotel room status display

| Specification      | Order No. | Packing unit | PS | EAN           |
|--------------------|-----------|--------------|----|---------------|
| cream white glossy | 3104 01   | 1            | 01 | 4010337042495 |
| pure white glossy  | 3104 03   | 1            | 01 | 4010337042501 |
| pure white matt    | 3104 27   | 1            | 01 | 4010337042525 |
| anthracite         | 3104 28   | 1            | 11 | 4010337042532 |
| colour aluminium   | 3104 26   | 1            | 11 | 4010337042518 |
| black matt         | 3104 005  | 1            | 11 | 4010337069812 |

### Features

- Switch for "Do not disturb" and "Make up room" hotel room status displays.
- With block to prevent both sides from being switched on.
- Locked both electrically and mechanically.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.

- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

---

## Technical data

Installation depth: 32 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

Rated output

- LEDi/CFLi: 100 W

---