

**Rocker switch insert 10 AX 250 V~ intermediate switch**

Specification	Order No.	Packing unit	PS	EAN
with mounting claws	3107 00	10/100	01	4010337039174
without mounting claws	3817 00	10	01	4010337039181

**Features**

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.

**Technical data****Installation depth**

- 3107 00: 32 mm
- 3817 00: 23 mm

**Connection cross section**

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

**Rated output**

- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated.
-