

## Pushbutton indicator switch insert 10 AX 250 V~ with orange LED lighting element 230 V~ circuit breaker, 2-pole

| Specification          | Order No. | Packing unit | PS | EAN           |
|------------------------|-----------|--------------|----|---------------|
| with mounting claws    | 3122 00   | 1            | 01 | 4010337038726 |
| without mounting claws | 3842 00   | 1            | 01 | 4010337064381 |

### Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technical data

#### Installation depth

- 3122 00: 32 mm
- 3842 00: 23 mm

#### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

#### Rated output

- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.
- 

## Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-