

**Hotel-card switch 10 A 250 V~  
1-pole NO contact with N terminal**

| Specification               | Order No. | Packing unit | PS | EAN           |
|-----------------------------|-----------|--------------|----|---------------|
| cream white glossy          | 3140 01   | 1            | 01 | 4010337042754 |
| pure white glossy           | 3140 03   | 1            | 01 | 4010337042761 |
| pure white matt             | 3140 27   | 1            | 01 | 4010337042785 |
| anthracite                  | 3140 28   | 1            | 11 | 4010337042792 |
| colour aluminium            | 3140 26   | 1            | 11 | 4010337042778 |
| black matt                  | 3140 005  | 1            | 11 | 4010337065104 |
| grey matt                   | 3140 015  | 1            | 11 | 4010337127154 |
| stainless steel (lacquered) | 3140 600  | 1            | 11 | 4010337045410 |

## Features

- The hotel-card switch can perform security and energy saving functions, for example.
  - When the hotel card is removed, any devices which are still switched on are deactivated.
  - The electric circuit is only activated via the button once the card has been inserted.
  - Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
  - Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- 

## Technical data

|  |                     |
|--|---------------------|
| Installation depth:                        | 32 mm               |
| Connection cross section                   |                     |
| - For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
| Rated output                               |                     |
| - LEDi/CFLi:                               | 100 W               |

---

## Notes

- Further versions are available upon request.
  - The screw-in clamp piece provides increased theft protection.
-