

**Rocker button insert 10 A 250 V~ NO contact, 1-pole with N terminal**

Specification	Order No.	Packing unit	PS	EAN
with mounting claws	3150 00	10/100	01	4010337038788
without mounting claws	3870 00	10/100	01	4010337064596

**Features**

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

**Technical data**

## Installation depth

- 3150 00: 32 mm
- 3870 00: 23 mm

## Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

**Notes**

- Can also be connected to be illuminated.