

**Rocker indicator switch insert 16 AX 250 V~  
with orange LED lighting element 230 V~  
universal off/2-way switch**

Specification	Order No.	Packing unit	PS	EAN
with mounting claws	3186 00	10	01	4010337124443

## Features

- For switching high loads
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

## Technical data

Installation depth:	32 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output	
- LEDi/CFLi:	100 W

## Notes

- Can also be connected to be illuminated.

## Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

---