

**Rocker with symbol
Light**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3285 01	1	01	4010337039600
pure white glossy	3285 03	10	01	4010337039617
pure white matt	3285 27	5	01	4010337039631
anthracite	3285 28	5	11	4010337039648
colour aluminium	3285 26	1	11	4010337039624
black matt	3285 005	5	11	4010337067757
grey matt	3285 015	1	11	4010337110460
stainless steel	3285 600	1	11	4010337044994

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-