

**Rocker with symbol  
Bell**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3286 01	1	01	4010337039723
pure white glossy	3286 03	10	01	4010337039730
pure white matt	3286 27	10	01	4010337039754
anthracite	3286 28	10	11	4010337039761
colour aluminium	3286 26	1	11	4010337039747
black matt	3286 005	5	11	4010337067870
grey matt	3286 015	1	11	4010337110477
stainless steel	3286 600	1	11	4010337045151

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
  - Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-