

## Rocker with control window

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3290 01	1	01	4010337041610
pure white glossy	3290 03	10/100	01	4010337041627
pure white matt	3290 27	10	01	4010337041641
anthracite	3290 28	10	11	4010337041658
colour aluminium	3290 26	1	11	4010337041634
black matt	3290 005	10	11	4010337067047
grey matt	3290 015	10	11	4010337110491
stainless steel	3290 600	1/5	11	4010337045403

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
  - Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-