

Rocker, 2-gang

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3295 01	10	01	4010337040811
pure white glossy	3295 03	10/100	01	4010337040828
pure white matt	3295 27	10	01	4010337040842
anthracite	3295 28	10	11	4010337040859
colour aluminium	3295 26	10	11	4010337040835
black matt	3295 005	10	11	4010337065616
grey matt	3295 015	10	11	4010337110514
stainless steel	3295 600	1/5	11	4010337045267

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-