

Rocker, 2-gang

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3295 01	10	01	4010337040811
pure white glossy	3295 03	10/100	01	4010337040828
pure white matt	3295 27	10	01	4010337040842
anthracite	3295 28	10	11	4010337040859
colour aluminium	3295 26	10	11	4010337040835
black matt	3295 005	10/100	11	4010337065616
grey matt	3295 015	10	11	4010337110514
stainless steel	3295 600	1/5	11	4010337045267

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-