

Rocker, 2-gang

| Specification | Order No. | Packing unit | PS | EAN |
|--------------------|-----------|--------------|----|---------------|
| cream white glossy | 3295 01 | 10 | 01 | 4010337040811 |
| pure white glossy | 3295 03 | 10/100 | 01 | 4010337040828 |
| pure white matt | 3295 27 | 10 | 01 | 4010337040842 |
| anthracite | 3295 28 | 10 | 11 | 4010337040859 |
| colour aluminium | 3295 26 | 10 | 11 | 4010337040835 |
| black matt | 3295 005 | 10 | 11 | 4010337065616 |
| grey matt | 3295 015 | 10 | 11 | 4010337110514 |
| stainless steel | 3295 600 | 1/5 | 11 | 4010337045267 |

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-