

Upright rocker with control window

Specification	Order No.	Packing unit	PS	EAN
pure white glossy	3490 03	1	01	4010337066705
pure white matt	3490 27	1	01	4010337066736
anthracite	3490 28	1	11	4010337066743
colour aluminium	3490 26	1	11	4010337066729
black matt	3490 005	1	11	4010337066668
grey matt	3490 015	5	11	4010337124245

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.

- LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-