

## Upright rocker

Specification	Order No.	Packing unit	PS	EAN
pure white glossy	3496 03	10	01	4010337121664
pure white matt	3496 27	10	01	4010337066101
anthracite	3496 28	10	11	4010337066262
colour aluminium	3496 26	1	11	4010337065999
black matt	3496 005	10	11	4010337065944
grey matt	3496 015	1	11	4010337110590
stainless steel	3496 600	1/5	11	4010337066279

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

- Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-