

## Cover with control window for pull-cord switch

| Specification      | Order No. | Packing unit | PS | EAN           |
|--------------------|-----------|--------------|----|---------------|
| cream white glossy | 3638 01   | 10           | 01 | 4010337042433 |
| pure white glossy  | 3638 03   | 10           | 01 | 4010337042440 |
| pure white matt    | 3638 27   | 1            | 01 | 4010337042464 |
| anthracite         | 3638 28   | 1            | 11 | 4010337042471 |
| black matt         | 3638 005  | 1            | 11 | 4010337064350 |

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.