

Cover with control window for pull-cord button

| Specification | Order No. | Packing unit | PS | EAN |
|--------------------|-----------|--------------|----|---------------|
| cream white glossy | 3639 01 | 1 | 01 | 4010337125877 |
| pure white glossy | 3639 03 | 1 | 01 | 4010337125884 |

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.