

## Rocker with control window and inscription space

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3670 01	1	01	4010337041740
pure white glossy	3670 03	1	01	4010337041757
pure white matt	3670 27	1	01	4010337041771
anthracite	3670 28	1	11	4010337041788
colour aluminium	3670 26	1	11	4010337041764
black matt	3670 005	1	11	4010337067078
grey matt	3670 015	1	11	4010337110569

### Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.

- Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- 

## Scope of supply

- Inscription labels with symbols "Light", "Call button" and "Door" are enclosed.
-