

Rocker with control window and symbol Light

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	3674 01	1	01	4010337041870
pure white glossy	3674 03	10	01	4010337041887
pure white matt	3674 27	10	01	4010337041993
anthracite	3674 28	10	11	4010337042099
colour aluminium	3674 26	1	11	4010337041894
black matt	3674 005	1	11	4010337067221
grey matt	3674 015	1	11	4010337110583

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-