

**SCHUKO socket outlet 16 A 250 V~with hinged cover, including sealing kit IP44 and cover frame  
Standard 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4157 01	1	01	4010337094500
pure white glossy	4157 03	1	01	4010337094517

**Features**

- UV-resistant
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

**Technical data**

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

**Notes**

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.

## Scope of supply

- Set of SCHUKO socket outlet with hinged cover, seal kit IP44 and cover frame Standard 55.

---