

## SCHUKO socket outlet 16 A 250 V~ Screw terminals

| Specification     | Order No. | Packing unit | PS | EAN           |
|-------------------|-----------|--------------|----|---------------|
| pure white glossy | 4180 70   | 1/5          | 01 | 4010337116998 |

### Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technical data

|                                                    |                                            |
|----------------------------------------------------|--------------------------------------------|
| Installation depth:                                | 29 mm                                      |
| Conductors:                                        | Rigid and flexible                         |
| Connection cross section<br>- for conductors from: | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |