

**SCHUKO socket outlet 16 A 250 V~  
with orange cover and imprint "ZSV" (additional safety power supply)**

Specification	Order No.	Packing unit	PS	EAN
orange glossy	4188 709	1/5	01	4010337117070

**Features**

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

**Technical data**

Installation depth:	32 mm
Conductors	
- Rigid and flexible:	
Connection cross section	
- for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

**Notes**

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- The bases of the SCHUKO socket outlets are colour coded accordingly.