

**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus)
without mounting claws, with screw terminals**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4383 01	1/5	01	4010337093633
pure white glossy	4383 03	1/5	01	4010337093657
pure white matt	4383 27	1/5	01	4010337108450
anthracite	4383 28	1/5	11	4010337093671
colour aluminium	4383 26	1/5	11	4010337093664
black matt	4383 005	1/5	11	4010337093626
grey matt	4383 015	1/5	11	4010337093640
stainless steel	4383 600	1/5	11	4010337093688

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature	
- increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-