

**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus)  
without mounting claws, with screw terminals**

| Specification      | Order No. | Packing unit | PS | EAN           |
|--------------------|-----------|--------------|----|---------------|
| cream white glossy | 4383 01   | 1/5          | 01 | 4010337093633 |
| pure white glossy  | 4383 03   | 1/5          | 01 | 4010337093657 |
| pure white matt    | 4383 27   | 1/5          | 01 | 4010337108450 |
| anthracite         | 4383 28   | 1/5          | 11 | 4010337093671 |
| colour aluminium   | 4383 26   | 1/5          | 11 | 4010337093664 |
| black matt         | 4383 005  | 1/5          | 11 | 4010337093626 |
| grey matt          | 4383 015  | 1/5          | 11 | 4010337093640 |
| stainless steel    | 4383 600  | 1/5          | 11 | 4010337093688 |

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technical data

|  |  |
|--|--|
| Installation depth:                                    | 32 mm                                      |
| Conductors:  | Rigid and flexible                         |
| Connection cross section<br>- for conductors from:     | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature<br>- increased contact protection: | 0°C to +45°C                               |

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-