

**SCHUKO socket outlet 16 A 250 V~ with hinged cover and increased contact protection (Safety Plus)  
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4414 01	1/5	01	4010337094388
pure white glossy	4414 03	1/5	01	4010337094401
pure white matt	4414 27	1/5	01	4010337094425
anthracite	4414 28	1/5	11	4010337094432
colour aluminium	4414 26	1/5	11	4010337094418
black matt	4414 005	1/5	11	4010337094371
grey matt	4414 015	1/5	11	4010337094395
stainless steel	4414 600	1/5	11	4010337094463

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technical data

Installation depth: 29 mm

Conductors

- Rigid and flexible:

Connection cross section

- for conductors from: 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>

---

## Notes

- Cover frames (1-gang to 5-gang) from the Standard 55, Gira E1 and Gira E2 design lines in combination with the sealing kit also suitable for the mounting of flush-mounted SCHUKO socket outlets with hinged cover in accordance with the IP44 protection rating.
  - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-