

**SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws
with green cover and imprint "SV" (safety power supply)**

Specification	Order No.	Packing unit	PS	EAN
green glossy	4418 107	1/5	01	4010337094951

Features

- Especially suited for angled plugs.
- Also for use in Gira energy profiles and underfloor systems.
- For screw mounting.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
- The bases of the SCHUKO socket outlets are colour coded accordingly.