

**SCHUKO socket outlet 16 A 250 V~ with orange control light and inscription space
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4452 01	1/5	01	4010337094630
pure white glossy	4452 03	1/5	01	4010337094654
pure white matt	4452 27	1/5	01	4010337094678
anthracite	4452 28	1/5	11	4010337094685
colour aluminium	4452 26	1/5	11	4010337094661
black matt	4452 005	1/5	11	4010337094623
grey matt	4452 015	1/5	11	4010337094647

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).

- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²

Scope of supply

- A neon lamp element is included with delivery.
 - Inscription label "EDV" is enclosed.
-