

**SCHUKO socket outlet 16 A 250 V~with hinged cover
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4454 01	1/5	01	4010337094029
pure white glossy	4454 03	1/5	01	4010337094050
pure white matt	4454 27	1/5	01	4010337094081
anthracite	4454 28	1/5	11	4010337094098
colour aluminium	4454 26	1/5	11	4010337094074
black matt	4454 005	1/5	11	4010337093992
grey matt	4454 015	1/5	11	4010337094043
stainless steel	4454 600	1/5	11	4010337094104

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²

Notes

- Cover frames (1-gang to 5-gang) from the Standard 55, Gira E1 and Gira E2 design lines in combination with the sealing kit also suitable for the mounting of flush-mounted SCHUKO socket outlets with hinged cover in accordance with the IP44 protection rating.