

**SCHUKO socket outlet 16 A 250 V~ without mounting claws
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4466 01	10	21	4010337095088
pure white glossy	4466 03	10	21	4010337095101
pure white matt	4466 27	10/100	21	4010337095125
anthracite	4466 28	10/100	11	4010337095132
colour aluminium	4466 26	10	11	4010337095118
black matt	4466 005	10/100	11	4010337095071
grey matt	4466 015	1/5	11	4010337095095
stainless steel	4466 600	10	11	4010337095149

Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
