

**Socket outlet with earth pin 16 A 250 V~
and increased contact protection (Safety Plus)
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4485 01	1/5	01	4010337095668
pure white glossy	4485 03	10/100	01	4010337095682
pure white matt	4485 27	10	01	4010337095712
anthracite	4485 28	10	11	4010337095729
colour aluminium	4485 26	10	11	4010337095705
black matt	4485 005	10	11	4010337095651
grey matt	4485 015	1/5	11	4010337095675
stainless steel	4485 600	1/5	11	4010337095736

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Replaces fully compatible 0485 ...:	
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature	
- increased contact protection:	0°C to +45°C

Notes

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-