

**Socket outlet with earth pin 16 A 250 V~
and increased contact protection (Safety Plus)**

Specification	Order No.	Packing unit	PS	EAN
pure white glossy	4485 70	1/5	01	4010337117971

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Approved in accordance with NF C 61-314:2017.
- Approved in accordance with NBN C 61-112-1:2017.
- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.