

**Socket outlet with earth pin 16 A 250 V~
and increased contact protection (Safety Plus)**

| Specification | Order No. | Packing unit | PS | EAN |
|-------------------|-----------|--------------|----|---------------|
| pure white glossy | 4485 70 | 1/5 | 01 | 4010337117971 |

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

| | |
|--|--|
| Installation depth: | 32 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - increased contact protection: | 0°C to +45°C |

Notes

- Approved in accordance with NF C 61-314:2017.
- Approved in accordance with NBN C 61-112-1:2017.
- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.