

**SCHUKO socket outlet 16 A 250 V~with hinged cover, lock and inscription space
with identical lock types**

| Specification | Order No. | Packing unit | PS | EAN |
|------------------|-----------|--------------|----|---------------|
| pure white | 4569 66 | 1 | 13 | 4010337094609 |
| anthracite | 4569 67 | 1 | 13 | 4010337094616 |
| colour aluminium | 4569 65 | 1 | 13 | 4010337094593 |

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

Technical data

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Height of the inscription label: | 12 mm |

Scope of supply

- Two keys are included with delivery.
 - Blank inscription label enclosed.
-