

SCHUKO socket outlet 16 A 250 V~with hinged cover, lock and inscription space with identical lock types

Specification	Order No.	Packing unit	PS	EAN
pure white	4569 66	1	13	4010337094609
anthracite	4569 67	1	13	4010337094616
colour aluminium	4569 65	1	13	4010337094593

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Height of the inscription label:	12 mm

Scope of supply

- Two keys are included with delivery.
 - Blank inscription label enclosed.
-