

**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus), without mounting claws
System 55**

Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4755 01	10	01	4010337093879
pure white glossy	4755 03	10	01	4010337093893
pure white matt	4755 27	10/100	01	4010337093916
anthracite	4755 28	10	11	4010337093923
colour aluminium	4755 26	1/5	11	4010337093909
black matt	4755 005	10	11	4010337093862
grey matt	4755 015	1/5	11	4010337093886

Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.

- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
 - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-