

eNet wireless diagnosis device

| Specification | Order No. | Packing unit | PS | EAN |
|---------------|-----------|--------------|----|---------------|
| | 5304 00 | 1 | 42 | 4010337774006 |

Features

- Display of the signal quality of selected eNet devices and status messages using LEDs.
- Display of wireless signals from non-eNet wireless transmitters.
- Switching the repeater function of mains operated actuators, transmitters, and energy sensors on or off.

Technical data

| | |
|----------------------|--------------------|
| Rated voltage: | DC 3 V |
| Battery | |
| - Type: | 1 x CR 2450N |
| - UN no.: | 3091 |
| Ambient temperature: | -5 °C to +45 °C |
| Wireless frequency: | 868.0 to 868.6 MHz |
| Range (free field): | approx. 100 m |

Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.
- Radio approval is valid for EU and EFTA countries.
- Diagnosis is only possible if wireless encryption (AES CCM 128) is inactive. Wireless encryption is activated or deactivated via the eNet server Version 2.0.

Scope of supply

- Batteries are included with delivery.