

## eNet Radio remote control, 1-gang

Specification	Order No.	Packing unit	PS	EAN
anthracite	5350 10	1	42	4010337774075

### Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- One button for one channel.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Operation locks.
- All-On or All-Off scenes and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

### Technical data

Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated voltage:	DC 3 V
Battery	
- Type:	CR 2450N
- UN no.:	3091
- W x H x D:	40,5 x 55 x 15 mm

## Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.
  - Radio approval is valid for EU and EFTA countries.
- 

## Scope of supply

- Batteries are included with delivery.
-