

eNet universal wireless transmitter, 2-gang Mini

Specification	Order No.	Packing unit	PS	EAN
	5453 00	1/5	42	4010337774310

Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- The eNet universal wireless transmitter enables the transmission of switching, dimming or blind commands to suitable eNet wireless receivers.
- Mounting in device box, surface-mounted housing or in installation adapter.
- Detection of voltage levels and changes at input.
- Connection of an external status LED.
- Indication of transmission status.
- Operating modes: 1-gang switching/dimming/blind, 1-gang automatic function, 2-gang switching/dimming/button operation, 2-gang automatic function.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- 2-gang blind.
- Operation locks.
- Establishing connections, enabled or disabled.
- Status for forced setting.
- All-On or All-Off scenes, threshold value scenes, and individual scenes can be configured.
- Configuration of scene button via eNet SMART HOME App (if-then rules) to trigger actions, scenes, or timers.
- Repeater function.
- Device software update.
- Localisation of the device.

Technical data

Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated voltage:	AC 110 V to 230 V, 50/60 Hz
Standby:	0.5 W
Inputs	
- Cable length:	Max. 100 m

Illustrations are similar and may deviate from originals.

- Input current:	2 mA
- Signal duration:	min. 200 ms
Output status LED	
- Rated voltage:	AC 110 V to 230 V
- Output current:	40 mA
Dimensions:	Ø 53,0 H 23,0 mm

Notes

- Radio approval is valid for EU and EFTA countries.
-