

## DCS-IP data interface

Specification	Order No.	Packing unit	PS	EAN
	5500 000	1	10	4010337052685

## Features

- The data interface is used to expand the current push-button start-up procedure by adding convenient start-up via PC/laptop and to connect the 2-wire bus to IP.
- Configuration via Gira Project Assistant (GPA).
- Start-up of large projects.
- Reading out of the configuration data of existing systems.
- Connection of Gira 2-wire bus to IP.
- Only suitable for indoor use.

## Technical data

Power supply	
- 2-wire bus:	DC 24 V $\pm$ 2 V
- Additional power supply:	DC 12 V to 26 V
- Current consumption:	max. 5 mA
Connections	
- 2-wire bus:	2 x plug terminal
- Additional power supply:	2 x plug terminal
Optical display	
- Mode:	orange
- Fct./Prog.:	green
IP communication:	Ethernet 10/100 BaseT (10/100 Mbit/s)
Ambient temperature:	-5 °C to +45 °C
Humidity:	93% rel. humidity
Protection class:	III (as per IEC 61140)

## Dimensions

Modular width (MW): 2

---