

**BNC insert, 2-gang**  
**Crimp connection**

Specification	Order No.	Packing unit	PS	EAN
pure white glossy	5630 03	1/5	01	4010337460251
black matt	5630 10	1/5	01	4010337460268

**Technical data**

Wave impedance:	50 $\Omega$
Installation depth:	25 mm

**Notes**

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40