

## Antenna socket insert (UD2415ST)

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	0042 00	1/5	31.97	01	4010337042006

### Features

- 2-gang routing box in plug-in technology.
- IEC plug for FM (radio) and DVB-T/T2.
- IEC pin jack for DVB-S/S2 (SAT).
- DC feed-through from the SAT connection to the input and bidirectional circulation between input and output with bridging of the DC voltage.
- The internal conductor is connected simply by pressing it, without the need for screws. Internal conductor can thus be removed multiple times.
- Complies with shield class A.

### Technical data

TV frequency band	
- Frequency range:	5 to 862 MHz
- Decoupling:	> 40 dB
- Transmission loss:	1.2 dB
- Attenuation: R/TV plug:	13 dB
SAT frequency band	
- Frequency range:	950 to 2400 MHz
- Decoupling:	> 35 dB
- Transmission loss:	2 dB
- Attenuation: SAT plug:	14 dB
Installation depth:	27 mm

### Notes

- Suitable for terrestrial reception, area couplers, and satellite reception systems.
- For screw attachment only.