

Gira E2 cover frame
pure white glossy

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--------------------------|-----------|--------------|------------------------|----|---------------|
| 1-gang | 0211 29 | 10/100 | 6.74 | 01 | 4010337211297 |
| 2-gang | 0212 29 | 10/100 | 9.25 | 01 | 4010337212294 |
| 2-gang, without crossbar | 1002 29 | 10 | 9.25 | 01 | 4010337001553 |
| 3-gang | 0213 29 | 1/5 | 16.88 | 01 | 4010337213291 |
| 4-gang | 0214 29 | 1/5 | 27.27 | 01 | 4010337214298 |
| 5-gang | 0215 29 | 1/5 | 41.61 | 01 | 4010337215295 |

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.